



# LEDEX™ WL-070+

LED dental curing light & wireless inductive charging stand



## Wireless inductive charging stand

No need to plug in the cable; No pogo pin required.



# ADVANTAGES

## Wireless inductive charging stand

No need to plug in the cable; No pogo pin required.

## Built-in intensity indicator

Easy to interpret due to the built-in intensity indicator.




Orange light  
 $\leq 700 \text{ mW/cm}^2$




Blue light  
 $> 700 \text{ mW/cm}^2$



### SE Standard Mode



### RA Ramp Mode



## Simple operations

Clear display with simple functions, including standard mode and ramp mode; easy to use.

## Cure fast in 10 secs

Having the high power 5W LED, this device can cure the composites over 3mm in 10 secs.

## Never shutdown after continuous use

Having the smart heat management system, the device will not be overheated after continuous use.



## Varieties of optical fiber light guide rod

There are 3,5, and 8 mm black or transparent optical fiber light guide rod to be applied.

## Specification

Handpiece	
Light source	High power dental blue 5 W LED, average lifespan is 100,000 hours
Wavelength	440-480 nm, peak:460 nm
Radiant intensity	up to 1200 mW/cm <sup>2</sup>
Light guide rod	Ø8mm optical fiber, Sterilizable in autoclave
Weight	120 g (with battery & light guide rod)
Dimensions	Ø 26 (max) x L156 mm

Battery	
Type	Lithium-ion, 3.7 V/800 mAh
Charge time	About 3 hours
Use time	40 Minutes (200 times in 10 Sec. mode)

Wireless charging stand	
Weight	85 g
Dimensions	W45 x L135 x H40 mm

Power Supply	
Type	Micro USB
Input	100~240 V, 50-60 Hz
Output	DC 5 V/2 A



+886 2-8976-9226 info@dentmate.com.tw  
 +886 2-8976-9236 www.dentmate.com.tw  
 8F, No.8-11, Sec 1, Zhongxing Road, Wugu District, New Taipei City 24872, Taiwan

